# Sterile Process Connection, Diaphragm Seals for Food, Biochemical and Pharmaceutical Industry Screwed Coupling Model 990.18 ... 990.21

WIKA Data Sheet DS 99.40



## Applications

- Food and beverage industry
- For dairies, dairy-products, breweries

### **Special Features**

- For cleaning easy to open
- Quick measuring point cleaning without residues
- Suitable for SIP and CIP
- 3A certified and FDA conformity
- Flush welded diaphragm



Diaphragm Seal, Model 990.18 with Union Nut and Pressure Gauge Model 232.50 NS 100



Diaphragm Seal with Union Nut according to standards SMS,

WIKA Data Sheet DS 99.40 · 10/2003



# Description

#### **Process connection**

#### Thread with union nut

Model 990.18: screwed coupling DIN 11 851 Model 990.19: screwed coupling SMS standard Model 990.20: screwed coupling IDF standard Model 990.21: screwed coupling APV-RJT standard Nominal sizes (DN) see dimensions overleaf

#### Pressure rating

PN 40 bar for DN 20 ... DN 50 resp. DN 1" ... DN 2" PN 25 bar from DN 65 resp. DN 21/2"

#### Suitable pressure ranges

0 ... 1 bar to 0 ... 25 resp. 40 bar

# Material of wetted parts

Stainless steel 1.4435 (316L)

#### Instrument connection

Pharmacopoeia (1998)

Gauges directly welded, transmitter with adaptor screwed

#### Fill fluid

KN 7 Glycerine, food compatible, FDA approved, according to standard US Pharmacopoeia XXIV and European **IDF and APV-RJT** 

Page 1 of 6



# **Optional extras**

#### **Process connection**

- Male thread
- Other nominal sizes (DN) and connections as per Südmo, BBS and further hygienic process connections on inquiry

#### **Pressure rating**

Higher pressure ratings on inquiry

#### Material of wetted parts

- Stainless steel 1.4435 electropolished
- Special materials on inquiry

#### Pressure instrument assembly

- Assembly via cooling tower
- Assembly via capillary, when ordering please specify: length of capillary

#### Fill fluid

- KN 62 Liquid Paraffin (medical white oil), pharmacompatible, FDA approved,
- KN 12 Glycerine/water, FDA approved

# Installation example for a diaphragm seal model 990.18 with union nut with direct mounted pressure gauge to a tube fitting with a corresponding male-thread



Pressure gauge Nominal size	Dimensions in mm Installation height h
NS 63	approx. 105
NS 100	approx. 156

The installation height is also valid for models 990.19, 990.20 and 990.21

## **Dimensions in mm**

#### Model 990.18 thread DIN 11 851



DN	For pipe Outside Ø x	PN	Dimensions	Dimensions in mm									Weight in kg	
	thickness		G	b	d	Mb	D	d3	d4	d <sub>6</sub>	е	f	g	
20	23 x 1.5	40	Rd 44 x 1/6	14	20	22	54	23	32.8	36,5	3	6	8	0.4
25	29 x 1.5	40	Rd 52 x 1⁄6	14	26	25	63	30	39.8	44	3.5	7	10	0.4
32	35 x 1.5	40	Rd 58 x 1⁄6	14	32	32	70	36	45.8	50	3.5	7	10	0.5
40	41 x 1.5	40	Rd 65 x 1⁄6	14	38	40	78	42	51.8	56	3.5	7	10	0.75
50	53 x 1.5	25	Rd 78 x 1/6	14	50	52	92	54	63.8	68,5	3.5	7	11	0.8
80	85 x 2	25	Rd 110 x ¼	20	81	71	127	85	94.8	100	3.5	8	12	1.25

The measuring instruments with model 990.18 can also be used for tubes acc. to DIN 11850 column 1 ... 3.

#### Model 990.19 thread SMS



DN	For pipe Outside Ø x	PN	N Dimensions in mm								Weight in kg	
	thickness		G	d	Mb	d <sub>1</sub>	d <sub>2</sub>	D	В	l <sub>1</sub>	l <sub>2</sub>	
<b>1½</b> "	38 x 1.2	40	Rd 60 x 1/6	35.6	35	48	55	74	25	15	4	0.8
2"	51 x 1.2	40	Rd 70 x 1⁄6	48.6	45	61	65	84	26	15	4	1.0

#### Model 990.20 thread IDF



DN	For pipe Outside Ø x	PN	Dimension	s in mm	Weight in kg				
	thickness		G	d	Mb	D	d <sub>1</sub>	d <sub>2</sub>	
<b>1</b> ½"	38,6 x 1.5	40	11⁄2" IDF	35.6	32	64	42.7	47	0.7
2"	51,6 x 1.5	40	2" IDF	48.6	45	79	56.2	60.5	0.9



DN	For pipe Outside Ø x	PN	Dimension	Dimensions in mm								Weight in kg
	thickness		G	d	Mb	d <sub>2</sub>	d <sub>3</sub>	D	l <sub>1</sub>	l <sub>2</sub>	SW	
11⁄2"	38.1 x 1.6	40	2 5/ <sub>16</sub> x 8"	34.9	32	40.5	54	25	14.3	2.4 4	65	0.9
2"	50.8 x 1.6	40	2 <sup>7</sup> / <sub>8</sub> x 6"	47.6	40	53.2	66.7	84	14.3	2.4 4	80	1.1

## **Possible combinations**

#### Bourdon tube pressure gauges

Diaphragm seal Model 990.18, 990.19, 990.20 or 990.21 can be combined with a pressure gauge with bourdon tube if the following application conditions are taken into account:

Pressure gauge directly combined with diaphragm seal

```
Temperature range
```

process: +10 ... +150 °C ambient: +10 ... +40 °C

Choice	Process connection with nominal sizes (DN)							
	20 32 (1½")	40 50 (2")	80 (3")					
Pressure gauge Model	23x.50.63	23x.50.63	23x.50.63					
	23x.50.100	23x.50/30.100	23x.50/30.100					
Lowest measuring range	0 4 bar	0 2 bar	0 0.6 bar					
	-1 3 bar	-1 3 bar	-1 1.5 bar					
Overpressure safety								
(optional)	-	2 x full scale value	2 x full scale value					
Inductive alarm sensors								
(optional), suitable in zone	-	possible	possible					
1 and zone 2 (Model 831)								

#### **Pressure transmitters**

Diaphragm seal Model 990.18, 990.19, 990.20 or 990.21 can be combined with a pressure transmitter Model S-10 or universal transmitter Model UT-10 if the following application conditions are taken into account:

Pressure transmitter directly combined with diaphragm seal

Temperature range

process: +10 ... +150 °C ambient: +10 ... +40 °C

Choice	Process connection with nominal sizes (DN)							
	20 25 (1")	32 (1 ½") 50 (2")	80 (3")					
Lowest measuring range	0 2.5 bar	0 1 bar	0400 mbar					

Further gauge variants and lower pressure ranges can be supplied after technical verification and clarification by WIKA.

#### **Ordering information**

Model / Process connection (with union nut or male thread) / Nominal sizes (DN) / Material of wetted parts / Assembly, if necessary length of capillary / Fill fluid / Pressure gauge model / Process conditions as per questionnaire / Optional extras resp. special version required

Modifications may take place and materials specified may be replaced by others without prior notice. Specifications and dimensions given in this leaflet represent the state of engineering at the time of printing.

Page 6 of 6

WIKA Data Sheet DS 99.40 · 10/2003



WIKA Alexander Wiegand GmbH & Co. KG Alexander-Wiegand-Straße 30 63911 Klingenberg/Germany Phone (+49) 93 72/132-0 Fax (+49) 93 72/132-406 E-Mail info@wika.de www.wika.de